

Feature	Availability	Comments	Added in the version
1) Pin type selection	Available	Have 19 selections	v1.0.00
2) Pin configuration	Only supports 1x1	Shows 4 pin configurations	v1.0.00
3) Selections of full micro plates	Available	To select source plates	v1.0.00
4) Display total number of samples Selected	Available		v1.0.00
5) Selection of spots per sample	Available		v1.0.00
6) Display total number of spots	Available	Displays total number of spots per print run	v1.0.00
7) Partial last micro plate	Available	Can select samples in last update	v1.0.00
8) Display last sampled well	Available		v1.0.00
9) Display cursor position	Available		v1.0.00
10) Import from sample pick file	Not available		v1.0.00
11) Selection of spot spacing	Available		v1.0.00
12) Selection of sub grid dimensions	Available	Can select up to 32x32	v1.0.00
13) Print offset selection	Available	Not recommended	v1.0.00
14) Sample loading time selection	Available		v1.0.00
15) Pre-printing and printing time Selection	Available		v1.0.00
16) Number of wash dry cycle selection	Available	For both end of print run and during printing	v1.0.00
17) Wash and dry duration selection	Available	For both end of print run and during printing	v1.0.00
18) Different wash and dry duration for Last cycle	Available	For both end of print run and during printing	v1.0.00
19) Display maximum printable Pre-print spots	Available		v1.0.00
20) Selection of pre-print spots per Sample	Available		v1.0.00
21) Display total number of pre-print Spots selected for the print run	Available		v1.0.00
22) Warning messages if selected amount exceeds available pre-print spots	Available		v1.0.00